

DN-FE-16T
Self adjusting
crimp tool

Rotatable die set,
front and side feed

Ergonomic,
strong & durable

Compact and
lightweight
design

Ratchet (with
emergency
release) to
ensure
completed
crimps

Low handle
force for strain
free crimping


Well balanced
- does not slip
out of the hand

Hole for
attaching a
safety strap



DN-FE-16T

Self-adjusting crimp tool
For insulated and non-insulated
ferules/wire end sleeves












Capacity:
0.14–10 mm²/AWG 26–8

MADE IN SWEDEN



Operating instructions
 Bedienungsanleitung
 Mode d'emploi
 Istruzioni per l'uso
 Instrucciones de empleo
 Gebruiksaanwijzing
 Bruksanvisning
 Χειρισμός
 Utilização



CAUTION
 VORSICHT
 ATTENTION

ATTENZIONE
 ATENCIÓN
 VOORZICHTIG

OBSERVER
 ΠΡΟΣΟΧΗ
 CUIDADO



Use safety Glasses to Avoid Eye Injury
 Benutzen Sie eine Sicherheitsbrille um Ihre Augen zu schützen
 Utiliser des lunettes de sécurité pour éviter une blessure aux yeux
 Usare gli occhiali di sicurezza per evitare il rischio di ferite agli occhi
 Se deben usar gafas de protección para evitar lesiones de la vista
 Draag ter voorkoming van oogletsel een veiligheidsbril
 Använd skyddsglasögon för att undvika ögonskador
 Χρησιμοποιείτε προστατευτικά γυαλιά για να μην τραυματίσετε τα μάτια σας
 Utilize óculos de proteção para evitar lesões nos olhos