

DC Output Modules

D3-04TD1 DC Output <--->	
Outputs per Module	4 (current sinking)
Commons per Module	4 (internally connected)
Operating Voltage	5-24VDC
Output Type	Field effect transistor
Peak Voltage	45VDC
AC Frequency	N/A
ON Voltage Drop	0.9V @ 6A
Max. Current	2A/point 6A/module
Max Leakage Current	0.4mA @ 40VDC
Max Inrush Current	6A/100ms
Minimum Load	5mA
Base Power Required	9V 12mA/pt (48mA Max) 24V 5mA
OFF to ON Response	0.1ms
ON to OFF Response	0.1ms
Terminal Type	Non-removable
Status Indicators	Logic side
Weight	4.2oz. (120g)
Fuses	4 (one 5A per common) user replaceable

D3-08TD1 DC Output <--->	
Outputs per Module	8 (current sinking)
Commons per Module	2 (internally connected)
Operating Voltage	5-24VDC
Output Type	NPN (open collector)
Peak Voltage	45VDC
AC Frequency	N/A
ON Voltage Drop	0.8V @ 0.5A
Max. Current	0.5A/point 1.8/common
Max Leakage Current	0.1mA @ 40VDC
Max Inrush Current	3A/20ms 1A/100ms
Minimum Load	1mA
Base Power Required	9V 20mA max 24V 3mA/pt (24mA Max)
OFF to ON Response	0.1ms
ON to OFF Response	0.1ms
Terminal Type	Non removable
Status Indicators	Logic side
Weight	4.2oz. (120g)
Fuses	2 (one 3A per common) non-replaceable

