

Wiring Accessories

Screwdrivers

Finally, a screwdriver made to comfortably fit the human hand! Our ergonomically designed, insulated slot head and Phillips screwdrivers are made from high quality heat-treated chrome vanadium steel with a black oxide coating on the tips for maximum corrosion protection. The screwdrivers are colored red for safety purposes and the one-piece blade insulation, which is integrally molded with the handle, also offers an extra measure of safety. You'll love the feel and the power of these durable tools.



Wire cutter/stripping tool

If you want to improve the speed, precision, and quality of your PLC or DINnectors wiring jobs, you'll want to order at least one of these self-adjusting wire cutter/stripping tools! This tool is suited for cutting/stripping PVC insulated round, oval or flat cables from 34 to 8 AWG without damaging the solid or stranded conductors. Its lightweight, ergonomic, soft rubber inlay, ergonomic handles are molded from super rugged glass-reinforced nylon, while the integral wire cutter and the replaceable blades are manufactured from high-grade hardened steel. With a higher mechanical advantage than any other competing tool, this wire stripper is the easiest on the installer's muscles!



Screwdriver Specifications			
Part #	Description/Dimensions (Dimensions in mm: tip thickness x tip width x blade length)	Pcs/Pkg	Price Each
DN-SS1	Insulated slotted screwdriver 0.4x2.5x75mm	1	<--->
DN-SS3	Insulated slotted screwdriver 0.5x3.5x100mm	1	<--->
DN-SS4	Insulated slotted screwdriver 0.8x4x100mm	1	<--->
DN-SS5	Insulated slotted screwdriver 1x5.5x125mm	1	<--->
DN-SP1	Insulated Phillips screwdriver #1x80mm	1	<--->
DN-SP2	Insulated Phillips screwdriver #2x100mm	1	<--->

Screwdriver Application Guide							
DINnectors & PLC Terminals	Slotted Screwdrivers				Phillips Screwdrivers		Hex Head
	DN-SS1	DN-SS3	DN-SS4	DN-SS5	DN-SP1	DN-SP2	
DN-D10		X					
DN-D10DR		X					
DN-D10L110		X					
DN-D10L24		X					
DN-D10LED1		X					
DN-D10X		X					
DN-DIS10			X				
DN-F6			X				
DN-F6L24			X				
DN-F6L110			X				
DN-F6L220			X				
DN-F10		X					
DN-F10L24		X					
DN-F10L110		X					
DN-F10L220		X					
DN-FM6			X				
DN-FM6-CC			X				
DN-FM6L			X				
DN-FM6L-CC			X				
DN-G1/0				X			
DN-G4				X			
DN-G6			X				
DN-G8			X				
DN-G10		X					
DN-KBD12	X						
DN-M10		X					
DN-M10B		X					
DN-MG10		X					
DN-T1/0				X			
DN-T1/0B				X			
DN-T3/0							X
DN-T3/0B							X
DN-T4				X			
DN-T4B				X			
DN-T6			X				
DN-T6B			X				
DN-T8			X				
DN-T8B			X				
DN-T10		X					
DN-T10B		X					
DN-T12	X						
DN-T12B	X						
DN-TL14	X						
DN-TL14S	X						
DN-TL14SLP	X						
DN-TL14SLN	X						
D2-8IOCON					X		
D2-16IOCON	X						
D3-16IOCON					X		
D4-16IOCON						X	

Wire Stripper Specifications			
Part #	Description	Pcs/Pkg	Price Each
DN-WS	Wire and cable, cut and strip tool, 28-10AWG	1	<--->
DN-WSJ	Replacement stripping jaws cartridge for DN-WS	1	<--->