

ACCESSORIES




CHAPTER 3

In This Chapter...

Accessories Overview.....	3-2
EA-ECOM Ethernet Communication Module.....	3-3
D-SUB 15-pin to Terminal Block Adapter	3-4
SD Card	3-5
USB FLASH Drive	3-5

Accessories Overview




Part Number	Description
EA-ECOM	Ethernet communication expansion module, (1) RJ45 10/100 Mbps Ethernet port.
EA-SD-CARD	SD memory card for non-volatile storage, 2GB industrial grade. 85°C maximum operating temperature makes it suitable for data logging in industrial applications.
USB-FLASH	USB Flash drive, SanDisk, 32GB
EA-COMCON-3A	DSUB port adapter, 15-pin male to 6-pole RS-422/485 terminal block, straight cable entry

EA-ECOM Ethernet Communication Module

The EA-ECOM Ethernet Communication module plugs into the expansion port on the *C-more* EA9-RHMI to allow a second Ethernet communication port for programming and PLC communications at a speed of 10/100 Mbps.

EA-ECOM



Dimensions: Inches [mm]

EA-ECOM Specifications

Part Number	EA-ECOM
Operating Temperature	0 to 50°C (32 to 122°F) Maximum surrounding air temperature rating: 50°C
Storage Temperature	-20 to +60°C (-4 to +140°F)
Humidity	5-95% RH (non-condensing)
Environmental Air	For use in pollution degree 2 environment
Vibration	IEC60068-2-6 (Test Fc), 5-9 Hz: 3.5 mm amplitude, 9-150 Hz: 1.0 G, sweeping, at a rate of 1 octave/min. (±10%), 10 sweep cycles per axis on each of 3 mutually perpendicular axes
Shock	IEC60068-2-27 (Test Ea), 15G peak, 11ms duration, three shocks in each direction per axis, on 3 mutually perpendicular axes (total of 18 shocks)
Noise Immunity	NEMA ICS3-304 RFI, (145MHz, 440MHz 10W @ 10cm) Impulse 1000V @ 1µs pulse
Emission	EN55011 Class A (Radiated RF emission)
Agency Approvals	CE (EN61131-2), UL508, CUL Canadian C22.2 To obtain the most current agency approval information, see the Agency Approval Checklist section on the specific part number's web page
Mounting Torque	50 oz-in [0.35 N-m]
Weight	0.23 lb [105g]
Ethernet Specification	Conforms to IEEE802.3
Communication Speed	10/100 Base-T (Automatic Negotiation)
Cable Specification	Category 5
Auto MDI / MDI-X	Yes
Connector Type	RJ45

D-SUB 15-pin to Terminal Block Adapter

The EA-COMCON-3A adapter is plugged into the 15-pin serial port on the front of the EA9-RHMI to allow wire terminal connections for RS-422/485 PLC communication cables.



EA-COMCON-3A is NOT UL Recognized or Listed.

EA-COMCON-3A



Dimensions

inches [mm]



SD Card

SD memory card for non-volatile storage, 2GB industrial grade. 85° C maximum operating temperature makes it suitable for data logging in industrial applications. Recommended for **C-more** EA9 series. The EA-SD-CARD utilizes SLC technology so it is the fastest option for writing and storing data. If logged data is saved to external memory, AutomationDirect recommends using an EA-SD-CARD.

EA-SD-CARD



NOTE: SLC Flash memory utilized by EA-SD-CARD has the advantage of being the most accurate flash memory type when reading and writing data. SLC flash has the longest lifespan of flash types and can operate in a broader temperature range than other types.

EA-SD-CARD with SLC Flash memory is recommended for industrial workloads that require heavy read/write cycles.

USB FLASH Drive

USB-FLASH sold by AutomationDirect has been tested with **C-more** HMIs and is Hi-Speed USB 2.0 certified. The EA-SD-CARD is the best option for logging data, but the USB-FLASH is a high quality flash drive perfect for transferring log files, capturing screens, backing up and restoring projects and storing images for the Image Viewer object.

USB-FLASH



