

USER MANUAL TABLE OF CONTENTS



NITRA PAL USER MANUAL

NITRA Pneumatic Automation Link User Manual	CF-1
Warnings and Trademarks	W-1
~ WARNING ~	W-1
Trademarks.	W-1
~ ADVERTENCIA ~	W-2
Marcas Registradas	W-2
~ AVERTISSEMENT ~	W-3
Marques de commerce	W-3
NITRA Pneumatic Automation Link User Manual Revision History.	H-1
NITRA Pneumatic Automation Link (PAL) Table of Contents	TOC-1
Chapter 1: Getting Started	1-1
Manual Overview	1-2
Overview of This Publication	1-2
Who Should Read This Manual	1-2
Supplemental Publications	1-2
Technical Support	1-2
Special Symbols	1-2
PAL System Introduction	1-3
Overview of the System	1-3
General Specifications	1-4
Components Overview.	1-5
Assembly.	1-10
Required Tools	1-10
Assembling the Bank.	1-10
Assembling the I/O Modules	1-12
Replacing the fittings	1-14
Replacing the Valves	1-15
Mounting the Bank to DIN Rail	1-16
Electrical Connections.	1-17
Power Wiring	1-17
PAL-EIP Connections.	1-19
Chapter 2: Conventional Electrical Modules	2-1
Conventional Electrical Modules.	2-2
Cables	2-2
Specifications.	2-3
Chapter 3: EtherNet/IP Modules	3-1
Overview	3-2

EtherNet/IP Modules	3-2
Specifications	3-2
System Setup For EtherNet/IP Assemblies	3-3
Initial Hardware Configuration	3-3
Configuring the PAL Network Settings	3-3
NITRA Pneumatic Automation Link (PAL) Configuration Software	3-6
EtherNet/IP Connections and Data Mapping	3-7
Chapter 4: I/O Modules	4-1
Overview	4-2
PAL-S01 8-point Discrete Input	4-2
Wiring Diagram.	4-2
Parameter Configuration.	4-3
Specifications	4-3
PAL-S02 8-point Discrete Output	4-4
Wiring Diagram.	4-4
Parameter Configuration.	4-4
PAL-S03 6-point Discrete Output + additional power connection	4-5
Wiring Diagram.	4-5
Parameter Configuration.	4-5
Specifications	4-6
PAL-S04 4-point Analog Input	4-6
Wiring Diagram.	4-7
Parameter Configuration.	4-7
Analog Input Data Format.	4-8
PAL-S05 4-point Analog Output	4-8
Wiring Diagram.	4-8
Parameter Configuration.	4-9
Specifications	4-10
PAL-S06 16-point Discrete Input.	4-10
Wiring Diagram.	4-10
Parameter Configuration.	4-11
PAL-S07 16-point Discrete Output.	4-12
Wiring Diagram.	4-12
Parameter Configuration.	4-12
Specifications	4-13
PAL-S08 4-point Analog Temperature Input	4-14
Wiring Diagram.	4-14
Parameter Configuration.	4-15
Specifications	4-17
Closed End Spacer Module.	4-18
Installation	4-18
Chapter 5: Pneumatic Modules	5-1
Overview	5-2
Primary Air Inlet / Exhaust Module	5-2
Intermediate Air modules.	5-3
Modular Valve Bases	5-5

Solenoid Valves	5-6
Valve Components and Materials of Construction	5-6
3-way valves	5-6
5-way valves	5-7
Special Purpose valve	5-8
Valve Flow Rates	5-8
Solenoid Valves Software Configuration Settings	5-8
PAL-Y38 Fitting	5-9
End Plates	5-10
PAL-C3 Wiring	5-10
Local Expansion Cables	5-10
Accessories and Replacement Parts	5-12
Air Connection Modules Accessories and Replacement Parts	5-12
Valve Base Accesories and Replacement Part	5-12
End Plate Accessory	5-12
Chapter 6: Stand-Alone Valve Bases	6-1
Overview	6-2
Port Connections	6-3
Wiring	6-4
Control Cables	6-4
Stand-Alone vs. PAL Assembly Comparison	6-5
Typical Stand-Alone Base Configuration	6-5
Comparable PAL Assembly Configuration	6-5
Mounting Options	6-6
DIN Rail Mounting	6-6
Bracket Mounting	6-6
LED Status Lights and Diagnostics	6-7
Chapter 7: Diagnostics / Troubleshooting	7-1
LED Status	7-2
Node Errors	7-3
System Diagnostics	7-4
Module LED Diagnostics	7-7
Solenoid Valve LED	7-7
Digital Input Module LEDs	7-7
Digital Output Module LEDs	7-7
Analog Input Module LEDs	7-7
Analog Output Module LEDs	7-8
Temperature Input Module LEDs	7-8

**BLANK
PAGE**