

# TABLE OF CONTENTS

---



|   |            |
|---|------------|
| User Caution .....                              | i          |
| Publication History.....                        | iv         |
| Table of Contents.....                          | vi         |
| <b>Chapter 1 - Getting Started.....</b>         | <b>1-1</b> |
| Introduction .....                              | 1-2        |
| Purpose of this Manual.....                     | 1-2        |
| About Getting Started .....                     | 1-2        |
| Online Help Files and Other Documentation.....  | 1-2        |
| Technical Support.....                          | 1-2        |
| Conventions Used.....                           | 1-3        |
| Key Topics for Each Chapter.....                | 1-3        |
| Before you begin... ..                          | 1-4        |
| Productivity Suite System Requirements.....     | 1-5        |
| Step 1: Install Programming Software.....       | 1-6        |
| Step 2: Launch Programming Software .....       | 1-10       |
| Online Help.....                                | 1-11       |
| Step 3: Install Hardware.....                   | 1-12       |
| Step 4: Apply Power to CPU .....                | 1-16       |
| Step 5: Establish PC to CPU Communications..... | 1-16       |
| Step 6: Open/Read Hardware Configuration.....   | 1-17       |
| Step 7: Create a Project.....                   | 1-19       |

## Table of Contents

---

|   |             |
|---|-------------|
| Step 8: Save Project.....                                 | 1-24        |
| Step 9: Write Project to CPU.....                         | 1-25        |
| Step 10: Place CPU in RUN Mode.....                       | 1-26        |
| Step 11: Test the Project Using Monitor Mode.....         | 1-27        |
| <b>Chapter 2 - Specifications.....</b>                    | <b>2-1</b>  |
| Overview.....   | 2-4         |
| Hardware.....   | 2-4         |
| <b>P1000 Power Supplies.....</b>                          | <b>2-5</b>  |
| P1-01AC and P1-02AC Power Supplies.....                   | 2-5         |
| P1-01AC Power Supply.....                                 | 2-6         |
| P1-02AC Power Supply.....                                 | 2-7         |
| Power Connections.....                                    | 2-8         |
| Grounding.....  | 2-8         |
| P1-01DC Power Supply.....                                 | 2-9         |
| Power Connections.....                                    | 2-10        |
| Grounding.....  | 2-10        |
| Productivity® 1000 Alternate Power Supply Connection..... | 2-11        |
| <b>Productivity® 1000 P1-540 CPU Module.....</b>          | <b>2-12</b> |
| P1-540 CPU Specifications.....                            | 2-12        |
| P1-540 CPU General Specifications.....                    | 2-13        |
| P1-540 Module Faceplate Layout.....                       | 2-14        |
| P1-540 Battery.....                                       | 2-15        |
| P1-540 Communication Ports.....                           | 2-16        |
| MicroUSB Programming Port.....                            | 2-16        |
| P1-540 Ethernet Port.....                                 | 2-17        |
| microSD Slot.....   | 2-18        |
| RS-232 Port.....  | 2-19        |
| P1-540 RS-485 Port.....                                   | 2-20        |
| RS-485 Port.....  | 2-20        |
| <b>Productivity1000 P1-550 CPU Module.....</b>            | <b>2-21</b> |
| P1-550 CPU Specifications.....                            | 2-21        |
| <b>Productivity1000 P1-550 CPU Module.....</b>            | <b>2-22</b> |

|  |             |
|--|-------------|
| P1-550 CPU Specifications.....                     | 2-22        |
| P1-550 Module Faceplate Layout .....               | 2-23        |
| P1-550 Battery .....                               | 2-24        |
| P1-550 Communication Ports.....                    | 2-25        |
| MicroUSB Programming Port .....                    | 2-25        |
| P1-550 Ethernet Port.....                          | 2-26        |
| microSD Slot.....                                  | 2-27        |
| RS-232 Port .....                                  | 2-28        |
| RS-485 Port.....                                   | 2-29        |
| <b>Remote Slave Module.....</b>                    | <b>2-30</b> |
| P1-RX Remote Slave Module.....                     | 2-30        |
| Status Indicators.....                             | 2-30        |
| P1-RX Power Terminal .....                         | 2-31        |
| P1-RX Remote I/O Example .....                     | 2-31        |
| P1-RX Setting Remote Slave Address .....           | 2-32        |
| P1-RX Remote I/O Port .....                        | 2-33        |
| <b>I/O Modules Overview .....</b>                  | <b>2-34</b> |
| <b>Discrete I/O Modules.....</b>                   | <b>2-35</b> |
| Discrete Input Modules.....                        | 2-35        |
| Discrete Output Modules.....                       | 2-35        |
| <b>Discrete Combo I/O Modules.....</b>             | <b>2-36</b> |
| Discrete Combo Input/Output Modules.....           | 2-36        |
| <b>I/O Modules Installation .....</b>              | <b>2-36</b> |
| <b>P1-08SIM Input Simulator Module.....</b>        | <b>2-37</b> |
| <b>P1-08ND-TTL DC Input.....</b>                   | <b>2-38</b> |
| Wiring Diagrams.....                               | 2-40        |
| <b>P1-08ND3 Sinking/Sourcing DC Input .....</b>    | <b>2-41</b> |
| Wiring Diagrams.....                               | 2-43        |
| <b>P1-16ND3 Sinking/Sourcing DC Input.....</b>     | <b>2-44</b> |
| Wiring Diagrams.....                               | 2-46        |
| <b>P1-08NE3 AC/DC Sinking/Sourcing Input .....</b> | <b>2-47</b> |
| Wiring Diagrams.....                               | 2-49        |
| <b>P1-16NE3 AC/DC Sinking/Sourcing Input.....</b>  | <b>2-50</b> |
| Wiring Diagrams.....                               | 2-52        |

## Table of Contents

---

|  |      |
|--|------|
| P1-08NA AC Input.....                      | 2-53 |
| Wiring Diagrams.....                       | 2-55 |
| P1-08TD-TTL DC Output.....                 | 2-56 |
| Wiring Diagrams.....                       | 2-58 |
| P1-08TD1 Sinking DC Output.....            | 2-59 |
| Wiring Diagrams.....                       | 2-61 |
| P1-08TD2 Sourcing DC Output.....           | 2-62 |
| Wiring Diagrams.....                       | 2-64 |
| P1-15TD1 Sinking DC Output.....            | 2-65 |
| Wiring Diagrams.....                       | 2-67 |
| P1-15TD2 Sourcing DC Output.....           | 2-68 |
| Wiring Diagrams.....                       | 2-70 |
| P1-08TA AC Output.....                     | 2-71 |
| Wiring Diagrams.....                       | 2-73 |
| P1-08TRS Isolated Relay.....               | 2-74 |
| Wiring Diagrams.....                       | 2-76 |
| P1-16TR Relay Output.....                  | 2-77 |
| Wiring Diagrams.....                       | 2-79 |
| P1-15CDD1 Input/Output.....                | 2-80 |
| Wiring Diagrams.....                       | 2-82 |
| P1-15CDD2 Input/Output.....                | 2-83 |
| Wiring Diagrams.....                       | 2-85 |
| P1-16CDR Discrete Input/ Relay Output..... | 2-86 |
| Wiring Diagrams.....                       | 2-88 |
| Analog I/O Modules Overview.....           | 3-3  |
| Analog I/O Modules.....                    | 3-4  |
| Analog Input Modules.....                  | 3-4  |
| Analog Output Modules.....                 | 3-4  |
| Analog Input/Output Modules.....           | 3-5  |
| P1-04AD Analog Input.....                  | 3-6  |
| Wiring Diagrams.....                       | 3-8  |
| Module Configuration.....                  | 3-9  |

**P1-04AD-1 Analog Input** ..... 3-10  
 Wiring Diagrams ..... 3-12  
 Module Configuration ..... 3-13

**P1-04AD-2 Analog Input**..... 3-14  
 Wiring Diagrams ..... 3-16  
 Module Configuration ..... 3-17

**P1-04ADL-1 Analog Input** ..... 3-18  
 Wiring Diagrams ..... 3-20  
 Module Configuration ..... 3-21

**P1-04ADL-2 Analog Input**..... 3-22  
 Wiring Diagrams ..... 3-24  
 Module Configuration ..... 3-25

**P1-08ADL-1 Analog Input** ..... 3-26  
 Wiring Diagrams ..... 3-28  
 Module Configuration ..... 3-29

**P1-08ADL-2 Analog Input**..... 3-30  
 Wiring Diagrams ..... 3-32  
 Module Configuration ..... 3-33

**P1-04RTD Analog Input**..... 3-34  
 Wiring Diagrams ..... 3-37  
 Module Configuration ..... 3-38

**P1-04THM Analog Input** ..... 3-39  
 Wiring Diagrams ..... 3-41  
 Module Configuration ..... 3-43

**P1-04NTC Thermistor**..... 3-44  
 Wiring Diagrams ..... 3-46  
 Module Configuration ..... 3-47

**P1-04DAL-1 Analog Output**..... 3-48  
 Wiring Diagrams ..... 3-50  
 Module Configuration ..... 3-51

**P1-04DAL-2 Analog Output** ..... 3-52  
 Wiring Diagrams ..... 3-54  
 Module Configuration ..... 3-55

## Table of Contents

---

|  |            |
|--|------------|
| P1-08DAL-1 Analog Output.....                              | 3-56       |
| Wiring Diagrams.....                                       | 3-58       |
| Module Configuration.....                                  | 3-59       |
| P1-08DAL-2 Analog Output.....                              | 3-60       |
| Wiring Diagrams.....                                       | 3-62       |
| Module Configuration.....                                  | 3-63       |
| P1-4ADL2DAL-1 Current Analog Input/Output.....             | 3-64       |
| Wiring Diagrams.....                                       | 3-67       |
| Module Configuration.....                                  | 3-68       |
| P1-4ADL2DAL-2 Voltage Analog Input/Output.....             | 3-69       |
| Wiring Diagrams.....                                       | 3-72       |
| Module Configuration.....                                  | 3-73       |
| Specialty Modules Overview.....                            | 4-2        |
| P1-02HSC High-Speed Isolated Sinking/Sourcing Input.....   | 4-3        |
| Wiring Diagrams.....                                       | 4-5        |
| Wiring Example for Koyo Open Collector Output Encoder..... | 4-6        |
| Wiring Example for Koyo Totem Pole Output Encoder.....     | 4-7        |
| Module Configuration.....                                  | 4-8        |
| P1-04PWM Module.....                                       | 4-9        |
| Wiring Diagrams.....                                       | 4-11       |
| Module Configuration.....                                  | 4-12       |
| High-Speed Module Tester Utility.....                      | 4-13       |
| <b>Chapter 5 - Installation and Wiring.....</b>            | <b>5-1</b> |
| <b>Safety Guidelines.....</b>                              | <b>5-3</b> |
| Plan for Safety.....                                       | 5-3        |
| Three Levels of Protection.....                            | 5-4        |
| Orderly System Shutdown.....                               | 5-4        |
| System Power Disconnect.....                               | 5-4        |
| Emergency Stop Circuits.....                               | 5-5        |
| <b>Productivity®1000 Mechanical Design.....</b>            | <b>5-6</b> |
| Typical Productivity1000 System.....                       | 5-6        |
| <b>Dimensions and Installation.....</b>                    | <b>5-7</b> |
| <b>Basic Dimensions.....</b>                               | <b>5-9</b> |
| P1-01AC, P1-02AC and P1-01DC.....                          | 5-9        |

P1-540/P1-550..... 5-9

P1-RX Module..... 5-10

I/O Modules..... 5-10

**Mounting Guidelines ..... 5-11**

    Enclosures...5-11

    Mounting Position..... 5-11

    Using Mounting Rails..... 5-11

    Mounting Clearances..... 5-12

    Temperature Considerations..... 5-12

    Power Considerations..... 5-12

    Grounding ..5-13

    Agency Approvals..... 5-13

    Installing the Power Supply..... 5-14

    DIN Rail Mounting P1000 System..... 5-15

    Surface Mounting P1000 System..... 5-15

    Installing the I/O Modules..... 5-16

**Wiring Guidelines ..... 5-17**

    Power Supply Wiring..... 5-17

    Grounding ..5-17

    Fuse Protection..... 5-18

**I/O Module Wiring Options..... 5-19**

    Hand Wiring System..... 5-19

    ZIPLink Wiring System..... 5-20

    Terminal Block With Pigtail Cable..... 5-20

    Input and Output Modules ZIPLink Selections..... 5-21

    Analog Modules ZIPLink Selections..... 5-22

    Removable Terminal Blocks (Optional)..... 5-23

    P1-10RTB and P1-10RTB-1 ..... 5-23

    P2-RTB and P2-RTB-1 ..... 5-23

    Terminal Block Installation..... 5-24

    Terminal Block Removal..... 5-25

    Planning the I/O Wiring Routes..... 5-25

**System Wiring Strategies..... 5-26**

    CPU Isolation Boundaries..... 5-26

    Sinking/Sourcing Concepts ..... 5-27

## Table of Contents

---

|   |             |
|---|-------------|
| I/O "Common Terminal" Concepts .....                                  | 5-28        |
| DC Input Wiring Methods.....  | 5-29        |
| DC Output Wiring Methods.....   | 5-29        |
| Relay Outputs - Wiring Methods.....                                   | 5-31        |
| Relay Outputs – Transient Suppression for Inductive Loads.....        | 5-32        |
| CPU's Integrated Transient Suppressors .....                          | 5-33        |
| Types of Additional Transient Protection.....                         | 5-34        |
| <b>Communications .....</b>   | <b>6-1</b>  |
| Communication Ports .....   | 6-1         |
| microSD Card:.....  | 6-2         |
| MicroUSB: ..6-2   |             |
| RS-232: .....6-2  |             |
| <b>Communications: Connectivity .....</b>                             | <b>6-8</b>  |
| CPU Port Connections .....  | 6-8         |
| ASCII and Custom Protocol Functionality.....                          | 6-13        |
| ASCII Instructions .....  | 6-13        |
| Custom Protocol Instructions.....                                     | 6-14        |
| <b>Communications: Ethernet.....</b>                                  | <b>6-16</b> |
| TCP and UDP Port Numbers .....  | 6-16        |
| IP Addressing and Subnetting .....                                    | 6-16        |
| PC Setup.....   | 6-17        |
| CPU Setup ..6-18  |             |
| CPU Setup, continued.....   | 6-19        |
| TCP Connection Behavior with Modbus TCP and Network Instructions..... | 6-19        |
| <b>Communications Modbus Functionality.....</b>                       | <b>6-20</b> |
| Master/Client Function Code and Data Type Support.....                | 6-20        |
| Slave/Server Function Code and Data Type Support.....                 | 6-22        |
| Assigning Modbus Addresses to Tags.....                               | 6-23        |
| Modbus Options.....   | 6-26        |
| Modbus Instructions .....   | 6-29        |
| Network Instructions.....   | 6-31        |
| Automatic Poll versus Manual Polling and Interlocking.....            | 6-32        |
| Message Queue .....   | 6-34        |
| <b>EtherNet/IP for the Productivity Series .....</b>                  | <b>6-35</b> |
| Terminology Definitions.....  | 6-35        |



|  |             |
|--|-------------|
| Network Layer Chart .....  | 6-36        |
| EtherNet/IP Data.....  | 6-36        |
| Class 1 and Class 3 Connections.....                             | 6-37        |
| Setup Example 1: Productivity® 1000 as EtherNet/IP Adapter ..... | 6-37        |
| Example 2: Productivity® 1000 as EtherNet/IP Scanner.....        | 6-40        |
| Troubleshooting Tips: .....                                      | 6-43        |
| EtherNet/IP I/O Message Troubleshooting:.....                    | 6-45        |
| EtherNet/IP Explicit Message Troubleshooting: .....              | 6-45        |
| ProNET .....   | 6-46        |
| Custom Protocol over Ethernet Functionality.....                 | 6-47        |
| Hardware Configuration .....                                     | 6-48        |
| Custom Protocol Ethernet Instruction.....                        | 6-49        |
| <b>Communications: Remote I/O and GS-Drives.....</b>             | <b>6-50</b> |
| Design Considerations for Remote I/O and GS-Drives.....          | 6-50        |
| <b>Communications: Port Configuration.....</b>                   | <b>6-56</b> |
| External Ethernet Port Settings.....                             | 6-57        |
| Local Ethernet Port Settings.....                                | 6-58        |
| Remote Access Configuration .....                                | 6-58        |
| Serial Configuration.....  | 6-59        |
| RS-232 and RS-485 Port Settings .....                            | 6-59        |
| <b>Communications: Error Codes.....</b>                          | <b>6-62</b> |
| <b>P1000 EtherNet/IP Error Codes .....</b>                       | <b>6-63</b> |
| <b>Chapter 7 - Maintenance and Troubleshooting .....</b>         | <b>7-1</b>  |
| <b>Hardware Maintenance.....</b>                                 | <b>7-3</b>  |
| Standard Maintenance .....                                       | 7-3         |
| Air Quality Maintenance.....                                     | 7-3         |
| CPU Battery Replacement.....                                     | 7-3         |
| <b>Diagnostics... 7-4</b>  |             |
| Diagnostics 7-4  |             |
| Critical Errors.....   | 7-4         |
| Non-Critical Errors.....   | 7-4         |
| Finding Diagnostic Information.....                              | 7-4         |
| Error Codes 7-4  |             |
| <b>CPU Functions Indicators .....</b>                            | <b>7-5</b>  |

## Table of Contents

---

|   |            |
|---|------------|
| PWR Indicator .....                                       | 7-6        |
| Faulty or Incorrect Power Supply .....                    | 7-6        |
| Faulty CPU ..   | 7-6        |
| Device or Module Causes the Power Supply to Shutdown..... | 7-7        |
| Run Indicator   | 7-8        |
| CPU Indicator   | 7-8        |
| Communications Problems .....                             | 7-8        |
| I/O Module Troubleshooting .....                          | 7-9        |
| Things to Check .....                                     | 7-9        |
| Error Codes   | 7-9        |
| Some Quick Steps .....                                    | 7-9        |
| Testing Output Points .....                               | 7-10       |
| Noise Troubleshooting .....                               | 7-11       |
| Electrical Noise Problems.....                            | 7-11       |
| Reducing Electrical Noise.....                            | 7-11       |
| Run Time vs. Stop Mode Transfer Instruction.....          | 7-12       |
| Run Time Transfers.....                                   | 7-13       |
| Stop Mode Transfers .....                                 | 7-13       |
| Forcing I/O Points.....                                   | 7-15       |
| Advantages of Forces .....                                | 7-15       |
| Enabling Forces .....                                     | 7-15       |
| Forcing Tags in Your System .....                         | 7-16       |
| Identifying Forced Values.....                            | 7-18       |
| Force Value Timing Chart.....                             | 7-19       |
| <b>Appendix A - European Union Directives (CE).....</b>   | <b>A-1</b> |
| European Union (EU) Directives.....                       | A-2        |
| Member Countries.....                                     | A-2        |
| Applicable Directives.....                                | A-2        |
| Compliance  | A-2        |
| General Safety.....                                       | A-4        |
| Special Installation Manual.....                          | A-4        |
| Other Sources of Information .....                        | A-4        |
| Basic EMC Installation Guidelines .....                   | A-5        |

Enclosures...A-5  
Mains Filters.....A-5  
Suppression and Fusing.....A-5  
Internal Enclosure Grounding.....A-5  
Equipotential Grounding.....A-5  
Communications and Shielded Cables.....A-6  
Analog and RS232 Cables.....A-7  
Multidrop Cables.....A-7  
Shielded Cables Within Enclosures.....A-7  
Analog Modules and RF Interference.....A-7  
Network Isolation.....A-8  
Items Specific to the Productivity® 1000.....A-9

**Appendix B - Productivity®1000 Error Codes..... B-1**

Communications Error Codes.....B-2  
Module Error Codes.....B-3  
CPU Error Codes.....B-4  
Project Error Codes.....B-5  
Project Error Messages.....B-7

**Appendix C - Security Considerations for Control Systems Networks..... C-1**

Security Considerations for Control Systems Networks..... C-2