

# TABLE OF CONTENTS

---



<b>Chapter 1 - Getting Started</b> .....	<b>1-1</b>
Productivity Suite System Requirements.....	1-3
Step 1: Install Programming Software.....	1-4
Step 2: Launch Programming Software.....	1-8
Step 3: Install Hardware.....	1-10
Step 4: Apply Power to CPU.....	1-13
Step 5: Establish PC to CPU Communications.....	1-14
Step 6: Open/Read Hardware Configuration.....	1-15
Step 7: Create a Project.....	1-17
Step 8: Save Project.....	1-23
Step 9: Write Project to CPU.....	1-24
Step 10: Place CPU in RUN Mode.....	1-25
Step 11: Test the Project Using Monitor Mode or Simulator.....	1-26
<b>Chapter 2 - Specifications</b> .....	<b>2-1</b>
Overview.....	2-3
P2-04B, P2-07B, P2-11B, P2-15B Bases.....	2-4
P2-01AC, P2-01DCAC, P2-01DC and P2-02DC Power Supplies.....	2-6
Productivity 2000 CPU Modules.....	2-12
P2-RS Remote Slave Module.....	2-31
I/O Modules Overview.....	2-40
Discrete I/O Modules.....	2-41
P2-08SIM Input Simulator Module.....	2-42

## Table of Contents

---

P2-08ND3-1 Sinking/Sourcing DC Input .....	2-43
P2-16ND3-1 Sinking/Sourcing DC Input.....	2-46
P2-32ND3-1 24VDC Sinking/Sourcing Input.....	2-49
P2-08NE3 AC/DC Sinking/Sourcing Input.....	2-52
P2-16NE3 AC/DC Sinking/Sourcing Input .....	2-55
P2-32NE3 AC/DC Sinking/Sourcing Input.....	2-58
P2-08NAS Isolated AC Input.....	2-61
P2-16NA AC Input.....	2-64
P2-08TD1S Isolated Sinking DC Output.....	2-67
P2-08TD2S Isolated Sourcing DC Output .....	2-70
P2-15TD1 Sinking DC Output.....	2-73
P2-15TD2 Sourcing DC Output.....	2-76
P2-08TD1P Sinking Protected DC Output .....	2-79
P2-08TD2P Sourcing Protected DC Output.....	2-82
P2-16TD1P Sinking Protected DC Output.....	2-85
P2-16TD2P Sourcing Protected DC Output.....	2-88
P2-32TD1P Sinking Protected DC Output .....	2-91
P2-32TD2P Sourcing Protected DC Output.....	2-94
P2-08TAS Isolated AC Output .....	2-97
P2-16TA AC Output .....	2-100
P2-08TRS Isolated Relay Output.....	2-103
P2-16TR Relay Output.....	2-106
<b>Chapter 3 - Analog I/O Specifications .....</b>	<b>3-1</b>
Analog I/O Modules Overview.....	3-3
Analog I/O Modules.....	3-4
Analog I/O Modules.....	3-5
P2-04AD Analog Input.....	3-6
P2-04AD-1 Analog Input.....	3-12

P2-04AD-2 Analog Input..... 3-17

P2-08AD-1 Analog Input..... 3-22

P2-08AD-2 Voltage Analog Input.....3-27

P2-08ADL-1 Current Analog Input ..... 3-32

P2-08ADL-2 Voltage Analog Input..... 3-36

P2-16AD-1 Current Analog Input..... 3-40

P2-16AD-2 Voltage Analog Input..... 3-45

P2-16ADL-1 Current Analog Input..... 3-50

P2-16ADL-2 Voltage Analog Input ..... 3-54

P2-06RTD Analog Input..... 3-58

P2-08THM Analog Input..... 3-65

P2-08NTC Thermistor .....3-72

P2-04DA Analog Output.....3-76

P2-04DA-1 Analog Output ..... 3-82

P2-04DA-2 Analog Output.....3-87

P2-04DAL-1 Analog Output ..... 3-92

P2-04DAL-2 Analog Output..... 3-96

P2-08DA-1 Current Analog Output..... 3-100

P2-08DA-2 Voltage Analog Output..... 3-105

P2-08DAL-1 Current Analog Output ..... 3-110

P2-08DAL-2 Voltage Analog Output ..... 3-114

P2-16DA-1 Current Analog Output..... 3-118

P2-16DA-2 Voltage Analog Output..... 3-123

P2-16DAL-1 Current Analog Output..... 3-128

P2-16DAL-2 Voltage Analog Output..... 3-132

P2-8AD4DA-1 Current Analog Input/Output ..... 3-136

P2-8AD4DA-2 Voltage Analog Input/Output..... 3-142

## Table of Contents

---

<b>Chapter 4 - Specialty Module Specifications .....</b>	<b>4-1</b>
Specialty Modules Overview.....	4-2
P2-HSI High-Speed Pulse Input Module .....	4-4
P2-HSO High-Speed Output Module .....	4-13
High-Speed Module Tester Utility.....	4-22
P2-02HSC High-Speed Counter Module .....	4-23
P2-04PWM Module.....	4-29
P2-SCM Module.....	4-33
P2-SCM Module Communications.....	4-35
<b>Chapter 5 - Installation and Wiring.....</b>	<b>5-1</b>
Safety Guidelines .....	5-2
Introduction .....	5-5
Dimensions and Installation .....	5-6
Mounting Guidelines .....	5-7
Wiring Guidelines .....	5-14
I/O Module Wiring Options.....	5-16
System Wiring Strategies.....	5-22
<b>Chapter 6 - Communications .....</b>	<b>6-1</b>
Communications .....	6-1
Communications: Connectivity .....	6-8
Communications: Ethernet.....	6-16
Communications Modbus Functionality.....	6-20
EtherNet/IP for the Productivity Series .....	6-35
Communications: Remote I/O and GS-Drives.....	6-50
Communications: Port Configuration.....	6-58
Communications: Error Codes.....	6-66

**Chapter 7 - Maintenance and Troubleshooting ..... 7-1**  
Hardware Maintenance ..... 7-2  
Diagnostics ..... 7-3  
CPU Indicators ..... 7-4  
PWR Indicator ..... 7-5  
Run Indicator ..... 7-7  
CPU Indicator ..... 7-7  
Communications Problems ..... 7-7  
I/O Module Troubleshooting ..... 7-8  
Noise Troubleshooting ..... 7-10  
Run Time vs Stop Mode Transfer Instruction ..... 7-11  
Forcing I/O Points ..... 7-14

**Appendix A - European Union Directives (CE)..... A-1**  
European Union (EU) Directives ..... A-2  
Basic EMC Installation Guidelines ..... A-4

**Appendix B - Productivity® 2000 Error Codes..... B-1**

**Appendix C - Security Considerations for Control Systems Networks..... C-1**  
Security Considerations for Control Systems Networks ..... C-2